




- In-Line Pressure Intensifier
- End pressure up to 2,000 bar / 29,000 psi (higher pressures possible)
- Multiple intensification ratios available
- Reciprocating - delivers continuous flow during pressure build up
- All high pressure valves are integrated

## The MP-2000 Pressure Intensifier

Ratio (i)	Max. Inlet flow (LPM / GPM)	Outlet Flow Q1 (LPM / GPM)	Outlet Flow Q2 (LPM / GPM)	Max. Supply Pressure (bar / psi)	Max. Output Pressure (bar / psi)
7.0	13.0 / 3.40	1.1 / 0.29	0.2 / 0.05	200 / 2,900	1,400 / 20,300
10.0	12.0 / 3.17	0.7 / 0.18	0.2 / 0.05	200 / 2,900	2,000 / 29,000
13.0	10.0 / 2.64	0.5 / 0.13	0.1 / 0.02	154 / 2,233	2,000 / 29,000
16.0	10.0 / 2.64	0.4 / 0.10	0.1 / 0.02	125 / 1,812	2,000 / 29,000

Weight : 2.7 kg



Dimensions in mm

**Ordering code**

MP-2000 - -

POV		Intensification			
Yes	S	7.0	10.0	13.0	16.0
No	P				

**Example**

MP-2000 with the POV integrated and intensification 10.0: MP-2000-P-10.0